







SURGE GUARD* MARINE POWER PROTECTION PRODUCTS

Bow to Stern Power Protection

Protect Your Investment. Today's watercraft contain sophisticated and sensitive electronics; a few short seconds of faulty power can damage expensive equipment and cause unsafe conditions in the

surrounding water that can lead to electrocution. Southwire's Surge Guard* power protection devices for marine products are designed to protect you and your watercraft from the potential dangers of faulty electrical

Surge Guard* Portable Power Protection for the Marine Industry

<p style="text-align: center;">30A Portable Surge Protector with GFI</p> 	<p style="text-align: center;">30A Entry Level Portable Surge Protector</p> 	<p style="text-align: center;">30A Portable Surge Protector with LCD Display</p> 	<p style="text-align: center;">50A Portable Surge Protector with LCD Display</p> 
<p>Model 67060</p> <ul style="list-style-type: none"> ■ Rated 120V, 30A - 10/3 AWG Cord ■ Automatically shuts off the power when ground faults are present ■ Protects against electrocution paralysis drowning ■ Requires manual reset after a ground fault ■ Marine connectors ■ Trips at 30mA ■ Weather and water resistant ■ 510 Joules of power surge protection 	<p>Model 67010</p> <ul style="list-style-type: none"> ■ Rated 120V, 30A ■ Identifies faulty pedestal power ■ 2100 Joules of surge protection ■ Analyzes circuits to verify pedestal power ■ Indicators illuminate to show power status ■ Tests for and indicates: <ul style="list-style-type: none"> • Open ground • Open neutral • Correct polarity ■ Marine connectors 	<p>Model 67030</p> <ul style="list-style-type: none"> ■ Rated 120V, 30A - 10/3 AWG Cord ■ Identifies faulty pedestal power ■ Continuously monitors for: <ul style="list-style-type: none"> • Voltage and amp draw • Reverse polarity (mis-wired pedestal, elevated ground voltage) ■ Compact and easy to use ■ 2450 Joules of surge protection ■ Automatic reset on power restoration ■ Shuts off power when the following is present: <ul style="list-style-type: none"> • Open neutral • Low (<102V) and high (>132V) voltage • Open ground • Reverse polarity • Miswired pedestal ■ Multi-mode surge suppression ■ 128 second reset delay protects A/C compressor ■ Marine connectors ■ Weather and water resistant 	<p>Model 67050</p> <ul style="list-style-type: none"> ■ Rated 120V, 50A - 6/4 AWG Cord ■ Identifies faulty pedestal power ■ Continuously monitors for: <ul style="list-style-type: none"> • Voltage and amp draw • Reverse polarity (mis-wired pedestal, elevated ground voltage) ■ Compact and easy to use ■ 3850 Joules of surge protection ■ Automatic reset on power restoration ■ Shuts off power when the following is present: <ul style="list-style-type: none"> • Open neutral • Low (<102V) and high (>132V) voltage • Open ground • Reverse polarity • Miswired pedestal • High current neutral ■ Multi-mode surge suppression ■ 128 second reset delay protects A/C compressor ■ Marine connectors ■ Weather and water resistant