

IMPORTANT SAFETY INSTRUCTIONS

MODEL #MH2021 SAVE THESE INSTRUCTIONS

WARNING – To reduce the risk of electric shock, disconnect the 12VDC power source prior to proceeding.

INSTALLATION INSTRUCTIONS

PLEASE READ THESE INSTRUCTIONS CAREFULLY.

In the event you have any questions concerning use or care of this product, please contact the sales department at Southwire Company, LLC.


SHORELINE REELS™ SWITCH KIT

Tools Required: Drill, Wire Strippers, Tape Measure, Phillips Screwdriver

Parts Included: MH2021

Installation Procedure

1. Identify area that switch plate (MH2021) is to be installed.
2. Mount the unit in the chosen location using applicable mounting hardware (not supplied). The mounting holes on the plate are 2.75" inches from center to center vertically and 1.50" inches from center to center horizontally. Holes in plate are sized for #6 mounting hardware.
3. Use wire diagram below to connect wire leads from unit to source power and to the reel unit. Only use applicable wire/connectors that are rated for the current draw of the reel. See reel unit instructions for more info.
4. Once unit is wired correctly reconnect the 12VDC power source previously disconnected. Test that the unit is properly wired by following the OPERATING INSTRUCTION steps listed in the reel instructions provide.



IMPORTANT SAFETY INSTRUCTIONS



Southwire™

Shoreline Reels™

RV, Marine, and Industrial

MODEL #MH2021

WARRANTY INFORMATION

Southwire Company, LLC warrants that its devices are free from defects in materials and workmanship for a period of one year from the date of original purchase. This one year warranty is in lieu of all other warranties, obligation, or liabilities expressed or implied by the company. Any properly installed device that proves defective in normal use will be repaired or replaced at Southwire's option provided the unit is returned through an authorized Southwire dealer or representative or ship the unit directly to Southwire following the procedure below:

1. Contact Southwire Customer Support at 1-800-780-4324 to obtain a Return Materials Number.
2. Properly package returned unit.
3. Display Return Materials Number on outside of box.
4. Include Proof of Purchase, including date of purchase.
5. Supply full written description of the problem.
6. Specify your name, address, and daytime phone number.
7. Ship unit postage prepaid directly to: **Return Materials Department - Southwire Company, LLC
4525 140th Avenue North, Suite 900 - Clearwater, Florida 33762**

Any questions regarding this warranty, please contact Southwire by phone at 1-800-780-4324

Warranty is void if the device has been altered, misused and/or abused in any way. Southwire cannot assume responsibility for customer alterations, acts of God, or any other factors not under the control of Southwire. Southwire cannot assume responsibility for damage in handling of shipment. Southwire shall have no responsibility for installation of this device or for any personal injury, property damage, any incidental, contingent, or consequential damages of any kind resulting in defects or failure of the unit to function in the event of a ground fault in the circuit it is protecting. Implied warranties (if any) including but not limited to implied warranties of fitness for a particular purpose and merchantability are limited in duration to a period ending one year from the date of original customer purchase. The exclusive remedy for breach of the limited warranty contained herein is the repair or replacement of the defective product at Southwire's option. In no case shall Southwire's liability under any other remedy prescribed by law exceed the purchase price. Some states do not allow the exclusion or limitation of incidental or consequen-

For technical assistance, please call 1-800-780-4324 x 20311

Manufactured by Southwire Company, LLC, 4525 140th Avenue North, Suite 900, Clearwater, Florida 33762

© 2017 Southwire Company, LLC. All rights reserved.

* Trademark of Southwire Company, LLC. Registered in the United States.

505-00108B